

DESCRIPTION

MLG-33 sealer (two- part seam sealer) is designed for **Mannington Assurance® II, BioSpec SR, Entwined Collection, Insight® Plus, Insight® Plus GB, Realities®, Relay®RE, Paradigm Collection and Vivendi II™ Collection** with low-gloss urethane-based wearlayers. A properly sealed seam will be as strong as the surface of the floor covering, and will remain intact for the life of the floor. The Versatile Sealing Tip (VST-96) is included in this kit.

DIRECTIONS

Prior to sealing, be certain all seams are clean, dry and free of adhesive contamination.

Part B, which contains the de-glossing agent, must be shaken vigorously before blending with Part A.

Empty entire contents of Parts A and B into the supplied applicator bottle. After securing the VST Tip to the applicator bottle, gently shake the bottle to mix the ingredients. After mixing, the bottle should stand until all trapped air bubbles have dispersed, typically 15 minutes.

Prior to use, check the flow of the sealer on a scrap piece of flooring.

Use the forefinger of one hand on top of the flat portion of the tip to guide and ensure proper fin penetration. Use the other hand to control sealer flow. Hold the bottle at approximately a 45° angle.

Lightly squeeze the bottle and apply a uniform bead of sealer approximately 1/8" wide centered on the seam cut.

Note: Do not insert fin into the seam on Mannington Assurance® II or BioSpec® SR. For Mannington Assurance® II or BioSpec® SR use the applicator with the fin up. Be sure that the sealer is in contact with both sides of the flooring.

Do not wipe the seam.

Allow the sealed seam to dry before traffic can be allowed on the floor. Do not walk on or move heavy furniture directly over the sealer until it is fully dry. We recommend 24 hours. Mark the seam by placing a scrap piece of flooring along each side of the seam.

COVERAGE

One kit of MLG-33 will seal approximately 70 lineal feet of seams.

PACKAGING

6 Kits per carton # 12212

STORAGE

Store in climate controlled interior locations. One year shelf life on unopened containers. MLG-33 cannot be saved for reuse. Safely discard any unused sealer.

PRECAUTIONS

- Flammable liquid.
- Do not use near heat, sparks, pilot lights, fire or other open flames.
- Do not ingest.
- Avoid contact with skin and eyes.
- Use in well-ventilated areas.
- Avoid prolonged breathing of vapors.
- Do not save for reuse.
- KEEP OUT OF THE REACH OF CHILDREN.

Choices that Work.

For more information, please contact Mannington Technical Services at 800 241 2262 Ext. 3 or visit www.manningtoncommercial.com.

May, 2016